

RAE Systems, Inc. 1339 Moffett Park Dr.

Telephone 408-752-0723 Tube Orders 1-888-723-8823 Sunnyvale, CA 94089 USA Web www.raesystems.com

Gas Detection Tube Data Sheet Acetone C₃H₆O No. 10-111-40

	Extended Range	Standard Range	Extended Range
Range (ppmv)	0.05 - 1%	0.1 - 2%	0.2 - 4%
No. of Pump Strokes	2	1	0.5
Sample Volume (mL)	200	100	50
Sample Time (min)	2 x 2	2	1.5
Correction Factor	0.5	1	2

Precision (Relative Standard Deviation)*: $\leq \pm 12\%$

Linearity with No. of Pump Strokes: $r^2 = 0.992$

Humidity: No effect 5 - 85% RH

Temperature Range: 0 - 40°C

(32 - 104°F)

Temp (°C/°F)	0/32	10/50	25/77	40/104
Corr. Factor	1.25	1.15	1.0	0.95

Storage Life: 2 years in darkness at 5 - 25°C (40 - 77°F). Refrigeration preferred.

Color Change: Orange → Black

<u>Reaction Principle</u>: $CH_3COCH_3 + Cr(VI) + H_2SO_4 \rightarrow Cr(III) + Oxidation Prods.$

Cross-sensitivity: Substance	Concentration (ppmv)	Apparent Reading*	Corr. Factor
Methyl ethyl ketone	0.6%	0.55%	1.1
Methyl propyl ketone	1.0%	0.65%	1.5
Methyl isobutyl ketone	1.0%	0.40%	2.5
CO	1.5%	0	-
CO ₂	1.5%	0	-
CH₄	2.5%	0	-
NH ₃	5.0%	1.4% brown	3.6
H ₂ S	300	0.5% diffuse#	-
Ethyl Acetate	1.0%	0.85% diffuse#	-
Hexane	0.24%	entire tube#	-
Isobutylene	0.20%	entire tube#	-
Toluene	400	0.3% diffuse#	-

^{*}Data based on RAE pumps and tubes used in standard range.

Other Possible Interferences: Other hydrocarbons.

Caution: Dispose of spent or expired tubes according to local regulations. Possibly hazardous materials are given under the section Reaction Principle.

[#] Faint black color over entire stain length. Ketones can be distinguished by their darker stains and sharp endpoints.